



B21D20D25CG1

by Burndy
Catalog ID: B21D20D25CG1

Flexible Copper Braid, 262 KCMIL, U - SHAPE

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810460382
UPC 12 Digit	7818104603822

Dimensions

Dimension - L Length Overall mm	514 mm
Dimension - Length Overall inch	20.25 in

Electrical Ratings

Rating - Indoor Amperage	304
Rating - Outdoor Amperage	364

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)