



## B21E12G22

by Burndy  
Catalog ID: B21E12G22

Prop 65 Notice

Flexible Copper Braid

## Product Details

### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810327371
UPC 12 Digit	7818103273711

### Dimensions

Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.00 in

### Electrical Ratings

Rating - Outdoor Amperage	400
---------------------------	-----

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)