



B22F124N

by Burndy
Catalog ID: B22F124N

FLEXIBLE COPPER BRAID.

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810049983
UPC 12 Digit	7818100499833

Dimensions

Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.00 in

Electrical Ratings

Rating - Outdoor Amperage	1100
---------------------------	------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)