



## B22F284N

by Burndy  
Catalog ID: B22F284N

FLEXIBLE COPPER BRAID.

## Product Details

### General

Connector Type	Braid
Material	Copper
UPC	781810308448
UPC 12 Digit	7818103084488

### Dimensions

Dimension - D inch	3.06 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	711 mm
Dimension - Length Overall inch	28.00 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	3.00 in

### Electrical Ratings

Amperage Rating	1100 A
-----------------	--------

### Certifications and Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)