



## B22G304N

by Burndy  
Catalog ID: B22G304N

Prop 65 Notice

Flexible Copper Braid

## Product Details

### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810242247

### Dimensions

Dimension - L Length Overall mm	762 mm
Dimension - Length Overall inch	30.00 in

### Electrical Ratings

Amperage Rating	1300 A
Rating - Outdoor Amperage	1300

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	2
-----------------------	---

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)