



B22G784NTN

by Burndy
Catalog ID: B22G784NTN

Prop 65 Notice

Flexible tinned copper braid 78.00"x3.00"x0.56"

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	4
UPC	781810657430
UPC 12 Digit	7818106574300

Dimensions

Dimension - L Length Overall mm	1981
Dimension - Length Overall inch	78
Dimension - Width inch	3
Dimension - Width mm	76 mm

Electrical Ratings

Amperage Rating	1300 A
-----------------	--------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)