



B238

by Burndy
Catalog ID: B238

Mold, Horizontal Cable Tap to Horizontal Cable Run, 3/0 AWG (Run), 1/0 AWG (Tap), 90 Weld Metal.

Features: Type BCC-2 Molds Are Used To Join Horizontal Cable Tap To A Horizontal Run Cable, Size Range Is 6 AWG Through 750 KCMIL Concentric Stranded Copper Conductors, Conductor Type: Concentric Stranded Copper, Recommended Accessories: B40-0319-03 Mold Cleaner For Cartridge Sizes #90 - #500, B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0330-00 Cable Clamp, Required Tools: B38-0309-00 Flint Ignitor, Cartridge Type: Standard

Product Details

General

Application	For Joining Horizontal Cable Tap To A Horizontal Run Cable
Sub Brand	BURNDYWELD
Type	Molds
UPC	781810378533
UPC 12 Digit	7818103785333

Conductor Related

Conductor - Copper Str Run	3/0 AWG
Conductor - Copper Str Run Range	3/0 AWG
Conductor - Copper Str Tap	1/0
Conductor - Copper Str Tap Range	1/0
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Run • CU C Str-Tap

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)