



# B2481

by Burndy  
Catalog ID: B2481

Concentric Stranded Copper Mold Connector, Conductor Size: 2 AWG, Pipe Size: 12 - 30 IN, Required Tools: B38-0309-00 Flint Ignitor.

Features: Type BCS-3 Molds Are Used To Join The End Of A Copper Cable At A 45 DEG Angle To A Vertical Steel Surface, Size Range Is #6 Through 1000 KCMIL Solid Copper Conductors, Pipe Size: 12 - 30 IN, Conductor Type: Concentric Stranded Copper, Required Tools: B38-0309-00 Flint Ignitor, Recommended Accessories: B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0101-00 Rasp, (2) B40-0106-27 20 Chain Extension

## Product Details

### General

Application	For Joining End Of A Copper Cable At A 45 DEG Angle To A Vertical Steel Surface
Sub Brand	BURNDYWELD
Type	Molds
UPC	781810460641

### Conductor Related

Conductor - Copper Str Run	2 AWG
Conductor - Copper Str Run Range	2 AWG
Conductor - Rigid Pipe Size	12 in-30 in
Conductor - Rigid Pipe Size Range	12 in-30 in
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• Pipe Rigid-Size</li> </ul>

### Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)