



B24G14D504NTN

by Burndy
Catalog ID: B24G14D504NTN

Prop 65 Notice

Tin Plated Ferrules

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	8
Plated	Y
UPC	781810327449
UPC 12 Digit	7818103274499

Dimensions

Dimension - L Length Overall mm	368 mm
Dimension - Length Overall inch	14.50 in

Electrical Ratings

Rating - Outdoor Amperage	2000
---------------------------	------

Certifications and Compliance

Standards - RoHS Compliance Status	EX
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)