



B264

by Burndy
Catalog ID: B264

Mold, Horizontal Cable Tap to Horizontal Cable Run, 350 kcmil (Run), 250 kcmil (Tap), 200 Weld Metal.

Features: Type BCC-2 Molds Are Used To Join Horizontal Cable Tap To A Horizontal Run Cable, Size Range Is 6 AWG Through 750 KCMIL Concentric Stranded Copper Conductors, Recommended Accessories: B40-0319-03 Mold Cleaner For Cartridge Sizes #90 - #500, B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0330-00 Cable Clamp, Conductor Type: Concentric Stranded Copper, Required Tools: B38-0309-00 Flint Ignitor, Cartridge Type: Standard

Product Details

General

| | |
|--------------|--|
| Application | For Joining Horizontal Cable Tap To A Horizontal Run Cable |
| Sub Brand | BURNDYWELD |
| Trade Name | BURNDYWeld® |
| Type | Molds |
| UPC | 781810379066 |
| UPC 12 Digit | 7818103790666 |

Conductor Related

| | |
|----------------------------|--|
| Conductor - Copper Str Run | 350 kcmil |
| Conductor - Copper Str Tap | 250 kcmil |
| Conductor Type | <ul style="list-style-type: none"> • CU C Str-Run • CU C Str-Tap |

Certifications and Compliance

| | |
|------------------------------------|----|
| Standards - RoHS Compliance Status | CM |
|------------------------------------|----|

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)