



## B2709

by Burndy  
Catalog ID: B2709

Mold, Horizontal to Horizontal Cable Cross, 4/0 AWG (Run), 2/0 AWG (Tap), 200 Weld Metal.

Features: Type Bcc-11 Molds Are Used To Join Uncut Horizontal Cables At Right Angles To Each Other, Size Range Is 6 AWG Through 500 KCMIL Concentric Stranded Copper Conductors, Conductor Type: Concentric Stranded Copper, Recommended Accessories: B40-0319-03 Mold Cleaner For Cartridge Sizes #90 - #500, B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0330-00 Cable Clamp, Cartridge Type: Standard

## Product Details

### General

|              |   |
|--------------|---|
| Application  | For Joining Uncut Horizontal Cables At Right Angles To Each Other |
| Sub Brand    | BURNDYWELD  |
| Trade Name   | BURNDYWeld®   |
| Type         | Molds   |
| UPC          | 781810383322  |
| UPC 12 Digit | 7818103833222   |

### Conductor Related

|                            |  |
|----------------------------|--|
| Conductor - Copper Str Run | 4/0 AWG  |
| Conductor - Copper Str Tap | 2/0 AWG  |
| Conductor Type             | <ul style="list-style-type: none"> <li>• CU C Str-Run</li> <li>• CU C Str-Tap</li> </ul> |

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Standards - RoHS Compliance Status | CM |
|------------------------------------|----|

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)