



B2747

by Burndy
Catalog ID: B2747

Mold, Horizontal to Horizontal Cable Cross, 500 kcmil (Run & Tap), 3-250 Weld Metal.

Features: Type Bcc-11 Molds Are Used To Join Uncut Horizontal Cables At Right Angles To Each Other, Size Range Is 6 AWG Through 500 KCMIL Concentric Stranded Copper Conductors, Recommended Accessories: B40-0319-01 Mold Cleaner For Cartridge Sizes #15 - #65, B40-0319-03 Mold Cleaner For Cartridge Sizes #90 - #500, B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0330-00 Cable Clamp, Conductor Type: Concentric Stranded Copper, Cartridge Type: Standard

Product Details

General

Application	For Joining Uncut Horizontal Cables At Right Angles To Each Other
Sub Brand	BURNDYWELD
Trade Name	BURNDYWeld®
Type	Molds
UPC	621945525047
UPC 12 Digit	7818103834388

Conductor Related

Conductor - Copper Str Run	500 kcmil
Conductor - Copper Str Tap	500 kcmil
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Run • CU C Str-Tap

Certifications and Compliance

Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)