



B2D10N

by Burndy
Catalog ID: B2D10N

Prop 65 Notice

Flexible Copper Braid

Product Details

General

Connector Type	Braid
Material	Copper
Physical Attribute - Number of Braids	2
UPC	781810454657
UPC 12 Digit	7818104546577

Dimensions

Dimension - D inch	3
Dimension - Hole Size inch	0.56
Dimension - L Length Overall mm	254
Dimension - Length Overall inch	10
Dimension - N inch	0.62
Dimension - Pad Width inch	0.94

Electrical Ratings

Rating - Indoor Amperage	380
Rating - Outdoor Amperage	455

Certifications and Compliance

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)