



B2D12W

by Burndy
Catalog ID: B2D12W

Prop 65 Notice

Tin Plated Ferrules

Product Details

General

| | |
|---------------------------------------|---------------|
| Connector Type | Braid |
| Material | Copper |
| Material - Ferrules | Y |
| Physical Attribute - Number of Braids | 2 |
| Plated | Y |
| UPC | 781810091845 |
| UPC 12 Digit | 7818100918455 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - D inch | 2.5 |
| Dimension - Hole Size inch | 0.44 |
| Dimension - L Length Overall mm | 305 mm |
| Dimension - Length Overall inch | 12.00 in |
| Dimension - N inch | 0.62 |
| Dimension - Pad Width inch | 0.94 |

Electrical Ratings

| | |
|---------------------------|-----|
| Rating - Indoor Amperage | 380 |
| Rating - Outdoor Amperage | 455 |

Certifications and Compliance

| | |
|-------------------------------|-------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |

| | |
|------------------------------------|-------|
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | EX |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)