

B2D19D42NTNCG1

by Burndy
Catalog ID: B2D19D42NTNCG1

Tin Plated Ferrules



Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810421017
UPC 12 Digit	7818104210177

Dimensions

Dimension - L Length Overall mm	493 mm
Dimension - Length Overall inch	19.39 in
Dimension - Pad Width inch	0.94
Weight	1.060 lb

Electrical Ratings

Rating - Indoor Amperage	380
Rating - Outdoor Amperage	395

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)