



## B2D24U

by Burndy  
Catalog ID: B2D24U

Undrilled Ferrules

## Product Details

### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810139875
UPC 12 Digit	7818101398755

### Dimensions

Dimension - D inch	2.50
Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	24.00 in
Dimension - N inch	0.62
Dimension - Pad Width inch	0.94

### Electrical Ratings

Rating - Indoor Amperage	380
Rating - Outdoor Amperage	455

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467

Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	25
-----------------------	----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)