



B2D36TNG89

by Burndy
Catalog ID: B2D36TNG89

Prop 65 Notice

Tin Plated Braid 36 X .63 X .25

Product Details

General

| | |
|---------------------|--------------|
| Material - Ferrules | Copper |
| UPC | 621945467064 |

Dimensions

| | |
|---------------------------------|-------|
| Dimension - L Length Overall mm | 914 |
| Dimension - Length Overall inch | 36 |
| Dimension - Width inch | 1.25 |
| Dimension - Width mm | 32 mm |
| Length | 36 in |

Electrical Ratings

| | |
|---------------------------|-----|
| Rating - Indoor Amperage | 380 |
| Rating - Outdoor Amperage | 455 |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 5 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)