

## B2D5D50G82

by Burndy  
Catalog ID: B2D5D50G82

Tinned flexible copper braid 5.50"x0.94"x0.25"



### Product Details

#### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	2
UPC	781810538555
UPC 12 Digit	7818105385555

#### Dimensions

Dimension - L Length Overall mm	140
Dimension - Length Overall inch	5.5
Dimension - Width inch	0.94
Dimension - Width mm	24 mm

#### Electrical Ratings

Rating - Indoor Amperage	380 A
Rating - Outdoor Amperage	455 A

#### Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM

#### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)