



## B2E14

by Burndy  
Catalog ID: B2E14

Prop 65 Notice

Flexible Copper Braid

## Product Details

### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	N
UPC	781810202470
UPC 12 Digit	7818102024700

### Dimensions

Dimension - D inch	3
Dimension - L Length Overall mm	356 mm
Dimension - Length Overall inch	14.00 in
Dimension - N inch	0.75
Dimension - Pad Width inch	1.62

### Electrical Ratings

Rating - Indoor Amperage	530
Rating - Outdoor Amperage	635

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)