



## B2E15G127TN

by Burndy  
Catalog ID: B2E15G127TN

Prop 65 Notice

Flexible tinned copper braid 15.00"x1.62"x0.25"

## Product Details

### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	2
UPC	781810543689
UPC 12 Digit	7818105436899

### Dimensions

Dimension - L Length Overall mm	381
Dimension - Length Overall inch	15
Dimension - Width inch	1.62
Dimension - Width mm	41 mm

### Electrical Ratings

Rating - Indoor Amperage	530 A
Rating - Outdoor Amperage	635 A

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)