



B2F106

by Burndy
Catalog ID: B2F106

Prop 65 Notice

Flexible Copper Braid

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Copper
Physical Attribute - Number of Braids	2
UPC	781810466162

Dimensions

Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	2692
Dimension - Length Overall inch	106
Thickness - Pad	0.38 in

Electrical Ratings

Rating - Indoor Amperage	600 A
Rating - Outdoor Amperage	720 A

Certifications and Compliance

Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)