



B2G16NSV

by Burndy
Catalog ID: B2G16NSV

Prop 65 Notice

Silver Plated Ferrules

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	2
Plated	Y
UPC	621945455719

Dimensions

Dimension - L Length Overall mm	406 mm
Dimension - Length Overall inch	16.00 in

Electrical Ratings

Rating - Indoor Amperage	700 A
Rating - Outdoor Amperage	840 A

Certifications and Compliance

Certification - CSA Approved	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)