

B2G30D81TNCG1

by Burndy
Catalog ID: B2G30D81TNCG1

Prop 65 Notice

Tin Plated Ferrules



Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	2
Plated	Y
UPC	781810420751
UPC 12 Digit	7818104207511

Dimensions

Dimension - L Length Overall mm	222 mm
Dimension - Length Overall inch	8.75 in
Weight	7.8 lb

Electrical Ratings

Rating - Outdoor Amperage	700
---------------------------	-----

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)