



## B32F32G20TN

by Burndy  
Catalog ID: B32F32G20TN

Prop 65 Notice

Tin Plated Ferrules

## Product Details

### General

|                                       |              |
|---------------------------------------|--------------|
| Connector Type                        | Braid        |
| Material                              | Copper       |
| Material - Ferrules                   | Y            |
| Physical Attribute - Number of Braids | 6            |
| Plated                                | Y            |
| UPC                                   | 621945454576 |

### Dimensions

|                                 |     |
|---------------------------------|-----|
| Dimension - L Length Overall mm | 813 |
| Dimension - Length Overall inch | 32  |

### Electrical Ratings

|                 |        |
|-----------------|--------|
| Amperage Rating | 1500 A |
|-----------------|--------|

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Standards - RoHS Compliance Status | CM |

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)