



B33F24N

by Burndy
Catalog ID: B33F24N

Prop 65 Notice

Flexible Tinned Copper Braid 24 X 3 X 0.62

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	9
UPC	781810551066
UPC 12 Digit	7818105510666

Dimensions

Dimension - L Length Overall mm	610
Dimension - Length Overall inch	24
Dimension - Width inch	3
Dimension - Width mm	76 mm

Electrical Ratings

Amperage Rating	2000 A
-----------------	--------

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)