

B33G334NTN

by Burndy
Catalog ID: B33G334NTN

Tin Plated Ferrules



Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	3
Plated	Y
UPC	781810427231
UPC 12 Digit	7818104272311

Dimensions

Dimension - L Length Overall mm	838 mm
Dimension - Length Overall inch	33.00 in

Electrical Ratings

Rating - Indoor Amperage	2500
Rating - Outdoor Amperage	3000

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)