



B33G394NTN

by Burndy
Catalog ID: B33G394NTN

Tin Plated Ferrules

Product Details

General

| | |
|---------------------------------------|---------------|
| Connector Type | Braid |
| Material | Copper |
| Material - Ferrules | Y |
| Physical Attribute - Number of Braids | 3 |
| Plated | Y |
| UPC | 781810427309 |
| UPC 12 Digit | 7818104273099 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - L Length Overall mm | 991 mm |
| Dimension - Length Overall inch | 39.00 in |

Electrical Ratings

| | |
|---------------------------|------|
| Rating - Indoor Amperage | 2500 |
| Rating - Outdoor Amperage | 3000 |

Certifications and Compliance

| | |
|------------------------------------|----|
| Standards - RoHS Compliance Status | CM |
|------------------------------------|----|

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)