



## B3E18NTN

by Burndy  
Catalog ID: B3E18NTN

Prop 65 Notice

Tin Plated Ferrules

## Product Details

### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	3
Plated	Y
Plating Type	Electro tin plated
UPC	781810086896
UPC 12 Digit	7818100868966

### Dimensions

Dimension - D inch	3 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	457 mm
Dimension - Length Overall inch	18 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	1.64 in
Dimension - Z inch	3.25 in
Thickness	0.31 in

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)