



B3G11N

by Burndy
Catalog ID: B3G11N

Prop 65 Notice

Flexible Copper Braid

Product Details

General

Connector Type	Braid
Material	Copper

Dimensions

Dimension - L Length Overall mm	279
Dimension - Length Overall inch	11

Electrical Ratings

Rating - Indoor Amperage	960 A
Rating - Outdoor Amperage	1150 A

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)