



## B3G12NTN

by Burndy  
Catalog ID: B3G12NTN

Prop 65 Notice

Tin Plated Ferrules

## Product Details

### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	3
Plated	Y
UPC	781810501092

### Dimensions

Dimension - L Length Overall mm	305
Dimension - Length Overall inch	12

### Electrical Ratings

Rating - Indoor Amperage	960 A
Rating - Outdoor Amperage	1150 A

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	48
-----------------------	----

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)