



B3G12SV

by Burndy
Catalog ID: B3G12SV

Copper Braid 12.12"x1.69"x0.69"

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	3
Plated	Y
Plating Type	Silver Plated
UPC	781810202654
UPC 12 Digit	7818102026544

Dimensions

Dimension - Hole Size inch	0.44 in
Dimension - L Length Overall mm	308 mm
Dimension - Length Overall inch	12.12 in
Dimension - Pad Width inch	1.69 in
Thickness	0.69 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)