



B3G20D50N

by Burndy
Catalog ID: B3G20D50N

Flexible Copper Braid

Product Details

General

| | |
|---------------------------------------|--------------|
| Connector Type | Braid |
| Material | Copper |
| Material - Ferrules | Y |
| Physical Attribute - Number of Braids | 3 |
| Plated | Y |
| UPC | 781810204467 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - L Length Overall mm | 521 mm |
| Dimension - Length Overall inch | 20.50 in |

Electrical Ratings

| | |
|---------------------------|------|
| Rating - Indoor Amperage | 960 |
| Rating - Outdoor Amperage | 1150 |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | EX |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)