



B4D14D25G40

by Burndy
Catalog ID: B4D14D25G40

Tinned Copper Braid 14.25"x1.19"x0.34"

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
Plating Type	Tin Plated
UPC	781810060995
UPC 12 Digit	7818100609955

Dimensions

Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	362 mm
Dimension - Length Overall inch	14.25 in
Dimension - Pad Width inch	1.19 in
Thickness	0.34 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)