



## B4D14W

by Burndy  
Catalog ID: B4D14W

Prop 65 Notice

Tinned Copper Braid 14"x1.19"x0.32"

## Product Details

### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
Plating Type	Tin Plated
UPC	781810202395
UPC 12 Digit	7818102023955

### Dimensions

Dimension - Hole Size inch	0.44 in
Dimension - L Length Overall mm	356 mm
Dimension - Length Overall inch	14.00 in
Dimension - Pad Width inch	1.19 in
Thickness	0.32 in

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)