



B4D24

by Burndy
Catalog ID: B4D24

Prop 65 Notice

Copper braid 24"x1.180"x0.340"

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Copper
Physical Attribute - Number of Braids	4
Plated	N
UPC	781810088845
UPC 12 Digit	7818100888455

Dimensions

Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	24
Dimension - Width inch	1.18

Electrical Ratings

Amperage Rating	600 A
-----------------	-------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	3
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)