



B4E18G88TN

by Burndy
Catalog ID: B4E18G88TN

Prop 65 Notice

Tinned copper braid 12"x1.64"x0.38"

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Tin Plated Copper
Physical Attribute - Number of Braids	4
UPC	621945457218
UPC 12 Digit	6219454572188

Dimensions

Dimension - Length Overall inch	12
Dimension - Width inch	1.64
Dimension - Width mm	42 mm

Electrical Ratings

Rating - Indoor Amperage	850 A
Rating - Outdoor Amperage	1020 A

Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)