

## B4E9D84CG1

by Burndy  
Catalog ID: B4E9D84CG1

Tin plated copper braid 9.84"X1.75"X0.38"



### Product Details

#### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Copper
Physical Attribute - Number of Braids	4
UPC	621945174160
UPC 12 Digit	6219451741600

#### Dimensions

Dimension - L Length Overall mm	250
Dimension - Length Overall inch	9.84
Dimension - Width inch	0.63
Dimension - Width mm	15.9 mm

#### Electrical Ratings

Rating - Indoor Amperage	850 A
Rating - Outdoor Amperage	1020 A

#### Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	UI

#### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)