



B4EE38TNCG1

by Burndy
Catalog ID: B4EE38TNCG1

Tin plated copper braid 38"x2.75"x0.54"

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Copper
Physical Attribute - Number of Braids	1
Plated	Y
UPC	781810420997
UPC 12 Digit	7818104209977

Dimensions

Dimension - L Length Overall mm	965 mm
Dimension - Length Overall inch	38
Dimension - Width inch	2.75
Weight	11.7 lb

Electrical Ratings

Amperage Rating	1500 A
Rating - Outdoor Amperage	1500

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)