



B4EE9D75TNCG1

by Burndy
Catalog ID: B4EE9D75TNCG1

Tin Plated Ferrules

Product Details

General

| | |
|---------------------------------------|---------------|
| Connector Type | Braid |
| Material | Copper |
| Material - Ferrules | Y |
| Physical Attribute - Number of Braids | 4 |
| Plated | Y |
| UPC | 781810420799 |
| UPC 12 Digit | 7818104207999 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - L Length Overall mm | 248 mm |
| Dimension - Length Overall inch | 9.75 in |

Electrical Ratings

| | |
|---------------------------|------|
| Rating - Outdoor Amperage | 1500 |
|---------------------------|------|

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)