



B4F13G78TN

by Burndy
Catalog ID: B4F13G78TN

Prop 65 Notice

Tin Plated Ferrules

Product Details

General

Connector Type	Braid
Material	Copper
UPC	781810474495
UPC 12 Digit	7818104744955

Dimensions

Dimension - L Length Overall mm	330.2 mm
Dimension - Length Overall inch	13 in

Electrical Ratings

Rating - Indoor Amperage	1200 A
Rating - Outdoor Amperage	1000 A

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)