



B4F28NTN

by Burndy
Catalog ID: B4F28NTN

Tin Plated Ferrules

Product Details

General

Connector Type	Braid
Material	Copper
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810513019
UPC 12 Digit	7818105130199

Dimensions

Dimension - L Length Overall mm	711
Dimension - Length Overall inch	28

Electrical Ratings

Rating - Indoor Amperage	1000 A
Rating - Outdoor Amperage	1200 A

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	4
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)