



## B4F90T12TNB

by Burndy  
Catalog ID: B4F90T12TNB

Prop 65 Notice

Belled, Tin Plated Ferrules

### Product Details

#### General

Connector Type	Braid
Insulation	Y
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
UPC	621945457355
UPC 12 Digit	6219454573555

#### Dimensions

Dimension - L Length Overall mm	2286
Dimension - Length Overall inch	90.00 in
Weight	22.474 lb

#### Electrical Ratings

Rating - Indoor Amperage	1000 A
Rating - Outdoor Amperage	1200 A

#### Certifications and Compliance

Certification - CSA Approved	Yes
UL Listed	Yes

#### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)