



## B4G12NNK

by Burndy  
Catalog ID: B4G12NNK

Nickel Plated Ferrules

### Product Details

#### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810257036
UPC 12 Digit	7818102570366

#### Dimensions

Dimension - L Length Overall mm	305 mm
Dimension - Length Overall inch	12.00 in

#### Electrical Ratings

Rating - Indoor Amperage	1200
Rating - Outdoor Amperage	1440

#### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

#### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)