



## B4G32D50

by Burndy  
Catalog ID: B4G32D50

Flexible Copper Braid

## Product Details

### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	N
UPC	781810087411
UPC 12 Digit	7818100874111

### Dimensions

Dimension - Hole Size inch	0.44 in
Dimension - L Length Overall mm	826 mm
Dimension - Length Overall inch	32.50 in
Dimension - Pad Width inch	1.69 in
Dimension - Z inch	3.25 in
Thickness	0.94 in

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)