



## B4G60N

by Burndy  
Catalog ID: B4G60N

Prop 65 Notice

Flexible Copper Braid

## Product Details

### General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
Plated	Y
UPC	781810375266
UPC 12 Digit	7818103752666

### Dimensions

Dimension - L Length Overall mm	1524 mm
Dimension - Length Overall inch	60.00 in

### Electrical Ratings

Rating - Indoor Amperage	1200
Rating - Outdoor Amperage	1440

### Certifications and Compliance

Standards - RoHS Compliance Status	EX
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)