



B4G72N

by Burndy
Catalog ID: B4G72N

Flexible Copper Braid

Product Details

General

Connector Type	Braid
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	4
UPC	781810493922
UPC 12 Digit	7818104939222

Dimensions

Dimension - L Length Overall mm	1829
Dimension - Length Overall inch	72.00 in

Electrical Ratings

Rating - Indoor Amperage	1200 A
Rating - Outdoor Amperage	1440 A

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	8
-----------------------	---

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)