



B500

by Burndy
Catalog ID: B500

Mold, Horizontal Cable Terminal to Ground Rod, 4/0 AWG, 90 Weld Metal, 1/2" Ground Rod.

Features: Type BCR-1 Molds Are Used To Terminate Horizontal Copper Cable At The Top Of A Vertical Ground Rod, Size Range Is 6 AWG Through 1000 KCMIL Concentric Stranded Copper Conductors, 1/2 IN Through 1 IN For The Ground Rod, Conductor Type: Concentric Stranded Copper, Ground Rod Size: 1/2 IN, Recommended Accessories: B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0304-00 File, B38-0330-00 Cable Clamp, Cartridge Type: Standard

Product Details

General

| | |
|--------------|---|
| Application | For Terminating Horizontal Copper Cable At The Top Of A Vertical Ground Rod |
| Sub Brand | BURNDYWELD |
| Trade Name | BURNDYWeld® |
| Type | Molds |
| UPC | 781810383711 |
| UPC 12 Digit | 7818103837111 |

Conductor Related

| | |
|----------------------------|--|
| Conductor - Copper Str Tap | 4/0 AWG |
| Conductor - Rod Size | 1/2 in |
| Conductor Type | <ul style="list-style-type: none"> • CU C Str-Tap • Rod-Size |

Certifications and Compliance

| | |
|------------------------------------|----|
| Standards - RoHS Compliance Status | CM |
|------------------------------------|----|

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)