



B6708

by Burndy
Catalog ID: B6708

Concentric Stranded Copper Mold Connector, Conductor Size: 600 KCMIL, Tools: B38-0309-00 Flint Ignitor, Accessories: B38-3922-00 Mold Cleaning Brush.

Features: Type BCS-3 Molds Are Used To Join The End Of A Copper Cable At A 45 DEG Angle To A Vertical Steel Surface, Size Range Is #6 Through 1000 KCMIL Solid Copper Conductors, Required Tools: B38-0309-00 Flint Ignitor, Recommended Accessories: B38-3922-00 Mold Cleaning Brush, B38-0135-00 Cable Cleaning Brush, B38-0101-00 Rasp, Conductor Type: Concentric Stranded Copper

Product Details

General

Application	For Joining End Of A Copper Cable At A 45 DEG Angle To A Vertical Steel Surface
Sub Brand	BURNDYWELD
Type	Molds
UPC	781810454183
UPC 12 Digit	7818104541833

Conductor Related

Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • Pipe Rigid-Size
----------------	--

Certifications and Compliance

Standards - RoHS Compliance Status	CM
------------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)