



## B7617

by Burndy  
Catalog ID: B7617

Mold, Horizontal Cable Tap to Horizontal Rebar Run, 2/0 AWG, #6 Rebar, 115 Weld Metal.

Weld Metal: 115, Handle clamps: B106

## Product Details

### General

|              |   |
|--------------|---|
| Application  | Recommended for right angle, horizontal connections for solid or concentric stranded conductors #6 through 4/0 joined to reinforcing bars #3 through #6 |
| Sub Brand    | EXOTHERMIC MOLDS  |
| Trade Name   | BURNDYWeld®   |
| Type         | Molds   |
| UPC          | 781810408865  |
| UPC 12 Digit | 7818104088655   |

### Conductor Related

|                                   |   |
|-----------------------------------|---|
| Conductor - Copper Str Size       | 2/0 AWG   |
| Conductor - Copper Str Size Range | 2/0 AWG   |
| Conductor - Rebar Size            | 6   |
| Conductor - Rebar Size Range      | 6   |
| Conductor Type                    | <ul style="list-style-type: none"> <li>• CU C Str-Size</li> <li>• Rebar-Size</li> </ul> |

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Standards - RoHS Compliance Status | CM |
|------------------------------------|----|

### Logistics

|                       |   |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)