



BA10E38

by Burndy
Catalog ID: BA10E38

Prop 65 Notice

Cu Terminal, Bulk, Ring Tongue, #12 - #10 AWG Str, 600 V, 3/8" stud, Polyvinylchloride Insulated, Yellow.

Features: Expanded Insulation Support Accepts Standard And Large Wire Diameters: Lowers Inventory Requirements, Permits Greater Flexibility And Provides Insulation Support, Funnel Entry: Easy Wire Insertion, Manufactured Of Pure Electrolytic Copper: Provides Maximum Conductivity, Low Resistance And Ductility For Excellent Crimp Forming Properties, Deep V Groove Serrations In The Inner Barrel: Provides Added Holding Strength And Better Conductivity, Electro-Tin Plated: Provides Durable Long-Lasting Corrosion Resistance, 600 V Maximum, 105 DEG C Maximum, Installation Tool: Plier Type: Y10D, Y10-22 Tool, Ratchet: MR8-89-1, MR15, M8ND Tool With N10HET-23 Die, Package: Bulk, Insulation Diameter (maximum): 0.26 IN, Color Code: Yellow, Wire Strip Length: 19/64 IN, Temperature Rating: 105 DEG C Maximum, Wire Insulation Grip: No, Finish: Electro-Tin Plated

Product Details

General

Application	For Commercial, Light Duty Industrial Control and Power Circuit Applications
Connector Type	Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUK
Trade Name	VINYLUK™
Type	Ring Tongue
UPC	781810026489
UPC 12 Digit	7818100264899

Dimensions

Dimension - Hole Size fraction	16/41
Dimension - Hole Size inch	0.39 in
Dimension - Length Overall inch	1.27 in
Dimension - Pad Width inch	0.53 in
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.45 in

Conductor Related

Conductor - Copper Str Size	12 AWG;10 AWG
Conductor - Copper Str Size Range	12 AWG-10 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	500
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)